



Technical Data Sheet



Technical Data Sheet
Ref: NRPTR10000
Issued: 07/10/2025
Number of pages: 3

Pritt Refill Flex Correction Roller



PRODUCT DESCRIPTION:

Pritt Refill Flex Correction Roller for instant correction and perfect results thanks to a smooth and clean application with a flexible nib. The roller is available in two different width 4.2mm & 6mm for machine or handwritten text. The corrected area can be overwritten without any drying time. The optimised correction layer shows outstanding smear resistance and coverage properties.

TECHNICAL PRODUCT DESCRIPTION:

Injection moulded plastic parts

- Pritt Compact Flex Correction Roller housing is made from 50% recycled plastic

Tape

- Siliconised polyester carrier
- Synthetic resin with titanium dioxide, cover up layer combined with a polyacrylate based adhesive

CHARACTERISTICS:

- Immediate coverage of nearly all types of writing, prints and drawings
- Flexible mini roller applicator for a smooth application and clean correction.
- Good adhesion on smooth and nearly smooth surfaces
- Two-way correction: pull for a whole sentence, push for one letter
- Cover up layer needs no drying time and can be overwritten with all common inks, pens and machines
- No smearing of water based inks on the cover up layer while overwriting
- No shadows on copies
- Writing tips or printing heads will not be damaged when applied correctly
- Solvent free



INSTRUCTIONS FOR USE:

Place paper/material to be corrected on a smooth, flat and steady surface.

Position the roller at a 45° angle over text to be corrected. Apply a light, but firm pressure on the roller nib and pull or push the roller over the surface you wish to correct. Make sure to put the application nib flat on the surface at every application. For a clean break, stop and lift up at a slight angle.

If the cover up layer should not stick properly to the paper, i.e. on critical coated papers the film may be finished with light pressure with your finger.

How to refill:

1. Retract nib
2. Press the button on the back
3. Refill cassette
4. Close device

TECHNICAL DATA

| | |
|-------------|--|
| Tape length | 12m |
| Tape width | 4.2mm & 6mm |
| Shelf Life | 2 years from date of manufacture @20°C |

LIMITATIONS

Storage

Store in a dry and cool place. Avoid temperatures over 50°C.

HEALTH AND SAFETY

Before using the product please see related Material Safety Data Sheet that is available on request.

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.



Henkel Norden AB

Box 1155, SE-172 23

Sundbyberg

SE: Tel. +46 10 480 75 00, DK: Tlf +45 4330 1300, NO: Tlf. +47 2337 1520, FI: Puh. +358 20 122 311

Consumer service

SE: Tel. 010 480 7601, DK: Tlf. 80 88 77 05, NO: Tlf. 800 191 00, FI: Puh. 0800 165 066

Consumerservice-ac.norden@henkel.com